




D7L2L1Z7L		Capacity	D1	D2	L	L1	L2	L3	L4	H	H1	H2	H3
	110kg-1.1t	250lb-2500lb	ø9	ø60	80	58	101.6	42.5	11	57.5	27.3	22	4.5
			[ø0.35]	[ø2.36]	[3.15]	[2.28]	[4.00]	[1.67]	[0.43]	[2.26]	[1.07]	[0.87]	[0.18]
	2.2t	5000lb	ø9	ø60	80	58	101.6	42.5	11	63.5	26.9	22	4.5
			[ø0.35]	[ø2.36]	[3.15]	[2.28]	[4.00]	[1.67]	[0.43]	[2.50]	[1.06]	[0.87]	[0.18]
	4.4t	10000lb	ø11	ø72	100	76	133.4	52.5	12	77.9	35.1	30	9.5
			[ø0.43]	[ø2.83]	[3.94]	[2.99]	[5.25]	[2.07]	[0.47]	[2.98]	[1.38]	[1.18]	[0.37]



NOTES:

- Dimensions are in mm[inches].
- Expansion+vibration kit may be rotated to any angle.

METTLER TOLEDO									
MTCN / MTCZ									
EXPANSION+VIBR KIT 0745									
72217274D									

GDL									
D	3010-093	60	2010.03.15						
C	3009-011	60	2009.02.04						
B	3008-070	60	2008.05.19						
VERIFICATION/RECORD NO				DATE/BY		DATE			
TEST/DRN		608		TEST/APPD					
CHECK/CHECK		607		CHECK/AGEN					
TIME/MFG		3-10		DATE/DATE		2007-09-03			
				S		A		N	
								1:1	
				SHEET: 第 1 页 of 共 1 页					